# TABLE TOP STERILIZER







# **Technical Specifications**

Model	Power	Voltage	Frequency	Tank Capacity	Appearance size	Inside Dimension	G·W
SUN-18-III	1800W	AC220V/110V ± 10%	50/60Hz ± 1Hz	18Litres	470X500X630	ф 249Х355	57kg
SUN-23-III	2000W	AC220V/110V ± 10%	50/60Hz ± 1Hz	23Litres	470X500X630	ф 249Х450	59kg
SUM-29-III	2200W	AC220V/110V ± 10%	50/60Hz ± 1Hz	29Litres	540X580X800	ф319X365	97kg
SUN-45-III	3500W	AC220V/110V ± 10%	50/60Hz ± 1Hz	45Litres	540X580X800	ф 319Х623	105kg

# **Product Features**

● 欧洲B级标准	● 三次脉动真空干燥	● 全电脑控制,D16位微处理器	● 强力散热系统	● 自动电子安全门锁
Lillian Marilana Dani'na			♦ 7 inch full-color touch	LCD screen.
Ultra Modern Design			◆ The operation is simp	ole, fast, be clear at a glance.
			0	

Opening Water Tank

- ♦ Opening storage tank, wastewater tank, easy to
- ◆ Large capacity,storage tank,waste water tank



Concealment Type Interface

- ◆ Drain valve, output interface conceal. Concise and easy appearance.
- ◆ Each interface front cover is open, easy to operate.

Test Function

- ◆ 1.B&D test, the steam leakage test.
- ◆ 2.Vacuum test, test the pot body tightness.

Recording Mode

- Built-in printer: End of the work, can automatically print work information, date and time.
- USB:Built USB interface, End of the work, the information stored in the U disk automatically.

Intelligent Identification Fault System

- Automatic identification of fault protection system, Safe and fast judgment fault.
- Semi-automatic fault identifying system. Judge incurable diseases quickly.



7' TFTLCD



Chamber punched by stainless steel (#304,thickness:2.5mm)



With international famous brand parts , of MOTOROLA, ST, ATMEL, DALLAS,OMRON and so on. Using fuzzy state control technology. Ensure the temperature correctly.





Open type water tank





## **Circuit Breaker**

Cuts off the external power supply during device malfunction to prevent fire.



# **Air Filter**

Filters airborne impurities into the chamber to prevent contamination.

# **Safety Valve**

Releases pressure overload, and restores idle chamber pressure when the chamber is overpressured.



**Two Condensers** 

Faster cooling; prolongs life time.

182 www.ajjhealthcare.com 183



# SEA23L/18L Sterilizer

















# Two types of record (Dual Recording)

- 1) USBMaster controller stores 2,000 fresh cycles: the data can be downloaded via USB. You can check and print all the records with a computer
- 2) Micro-Printer(Optional) Prints cycle data when the cycle ends.



# **Big Capacity Open Tank**

- 1) Open tank, easy-to-clean.
- 2) Built-in water quality sensor monitors water quality reduces machine failure rate, and prolongs machine lifetime



# **Suitable for Different Types Instruments**

Surgical instruments, dental instruments, glass wares, injection units and other objects of compression resistance and hot steam resistance.

















#### SEA-18L-D

Model	Voltage	Power	Capacity	Chamber Size	Product Size	Weight
	V/Hz	W	L	mm	mm	N.W(Kgs)
SEA18	230/50	1800	18	Ø 249X355	594X468X453	47



#### SEA-23L-D

Model	Voltage	Power	Capacity	Chamber Size	Product Size	Weight
	V/Hz	W	L	mm	mm	N.W(Kgs)
SEA23	230/50	1800	23	Ø249X450	594X468X453	50



#### SEA-29L-D

Model	Voltage	Power	Capacity	Chamber Size	Product Size	Weight
	V/Hz	W	L	mm	mm	N.W(Kgs)
SEA29	230/50	2500	29	Ø319X420	535X650X505	80



ı	Model	Voltage	Power	Capacity	Chamber Size	Product Size	Weight
		V/Hz	W	L	mm	mm	N.W(Kgs)
	SEA45	230/50	3300	45	Ø 319X620	535X850X505	92



Model	Voltage	Power	Capacity	Chamber Size	Product Size	Weight
	V/Hz	W	L	mm	mm	N.W(Kgs)
SEA16-N-LED	230/50	1800	16	Ø 230X370	435X532X390	26

www.ajjhealthcare.com 185





#### SEA-23L-B-LCD/SEA-18L-B-LCD

Model	Voltage	Power	Capacity	Chamber Size	Product Size	Weight
	V/Hz	W	L	mm	mm	N.W(Kgs)
SEA23-B-LCD	230/50	1800	23	Ø 249X450	594X468X453	50
SEA18-B-LCD	230/50	1800	18	Ø 249X355	594X468X453	47



#### SEA-23L/18L-B-LED (Printer)

Model	Voltage	Power	Capacity	Chamber Size	Product Size	Weight
	V/Hz	W	L	mm	mm	N.W(Kgs)
SEA23-B-LED	230/50	1800	23	Ø 249X450	594X468X453	50
SEA18-B-LED	230/50	1800	18	Ø 249X355	594X468X453	47



## SEA-23L-B-LED/SEA-18L-B-LED

Model	Voltage	Power	Capacity	Chamber Size	Product Size	Weight
	V/Hz	W	L	mm	mm	N.W(Kgs)
SEA23-B-LED	230/50	1800	23	Ø 249X450	594X468X453	50
SEA18-B-LED	230/50	1800	18	Ø 249X355	594X468X453	47



# SEA-23L-N-LED / SEA-18L-N-LED

Model	Voltage	Power	Capacity	Chamber Size	Product Size	Weight
	V/Hz	W	L	mm	mm	N.W(Kgs)
SEA23-N-LED	230/50	1800	23	Ø 249X450	580X460X450	33
SEA18-N-LED	230/50	1800	18	Ø 249X450	580X460X450	30



#### SEA-12L-B-LED

Model	Voltage	Power	Capacity	Chamber Size	Product Size	Weight
	V/Hz	W	L	mm	mm	N.W(Kgs)
SEA12-B-LED	230/50	1800	12	Ø 200X360	560X439X369	42

# **Accessory Devices**



## Water Distiller——Drink

Power supply: 110V/230V, 50Hz

Output water: 1L/H
Net weight: 4.2Kg

Chamber dimension: 180X200mm

Machine dimension: 260X220X380mm



## Lubrication Device –LUB90(B)

Power supply: 110V/230V, 50Hz Air consumption: 60L/Min Power air sources: 0.3-0.6Mpa

Connectors for handpiece; high speed \*2

Low speed \*1

Net weight: 7.2Kg

Product dimension: 280X300X370mm



( With Paper Rolling Shelf )

# Sealing Machine—SEAL120

Power: 100W

Power supply: 230V,50~60Hz Net weight: 7kg(4.8kg)

Sealing temperature: 200 °C ± 10 °C Width of indentation: 12mm

Package size: 500X400X250mm

Max width of seal: 300mm

186 www.ajjhealthcare.com 187